



ITEM	QTY	DESCRIPTION	MFG	CATALOG
01	1	CONCEPT WALL-MOUNT ENCLOSURE	HOFFMAN	CSD20248
02	1	24" X 20" SUBPAN	HOFFMAN	CP2420
03	7	1X4 GRAY SLOT WIRE DUCT	PANDUIT	F1X4LG6
04	1	PANEL GROUND LUG #8AWG	ILSCO	TA-2
05	1	2 POLE FUSE BLOCK - CLASS CC	AB	1492-FB2C30-L
06	1	1 POLE FUSE BLOCK - CLASS CC	AB	1492-FB1C30-L
07	A/R	RAIL, DIN MTG, 25MM, 1M	AB	199-DR1
08	8	END ANCHOR	AB	1492-EAJ35
09	6	SCREW CONNECTION TERMINAL BLOCK; 1492-J	AB	1492-J4
10	1	END BARRIER; 1492-J	AB	1492-EBJ3
11	3	GROUP MARKER CARRIER	AB	1492-GM35
12	2	1AMP CIRCUIT BREAKER	AB	1492-SP1D010
13	1	PS, COMPACT, 30 W, 24-28V	AB	1606-XLP30E
14	1	INDUSTRIAL, COPPER TO FIBER MEDIA CONVERTER 10-/100-MBPS	BLACKBOX	LIC022A
16	1	ENERGY MONITOR EM3, 120/240VAC, SERIAL RS-485	AB	1408-EM3A-ENT
17	1	SHORTING BLOCK, 8 POSITION	FLEX-CORE	IKU8SC
18	1	GROUNDING BAR SYSTEM, 9 POS	SQUARE-D	PK9GTA
19	1	3 POLE FUSE BLOCK - CLASS CC	AB	1492-FB3C30-L