



ITEM	QTY	DESCRIPTION	MFG	CATALOG
01	1	CONCEPT WALL-MOUNT ENCLOSURE	HOFFMAN	CSD20248
02	1	24" X 20" SUBPAN	HOFFMAN	CP2420
03	A/R	1X4 GRAY SLOT WIRE DUCT	PANDUIT	F1X4LG6
04	1	PANEL GROUND LUG #8AWG	ILSCO	TA-2
05	1	2 POLE FUSE BLOCK - CLASS CC	AB	1492-FB2C30-L
06	1	1 POLE FUSE BLOCK - CLASS CC	AB	1492-FB1C30-L
07	A/R	RAIL, DIN MTG, 25MM, 1M	AB	199-DR1
08	6	END ANCHOR	AB	1492-EAJ35
09	6	SCREW CONNECTION TERMINAL BLOCK; 1492-J	AB	1492-J4
10	1	END BARRIER; 1492-J	AB	1492-EBJ3
11	4	GROUP MARKER CARRIER	AB	1492-GM35
12	2	1AMP CIRCUIT BREAKER	AB	1492-SP1D010
13	1	PS, COMPACT, 30 W, 24-28V	AB	1606-XLP30E
14	1	INDUSTRIAL, COPPER TO FIBER MEDIA CONVERTER 10-/100-MBPS	BLACKBOX	LIC022A
16	1	POWER MONITOR 3000, 120V/240VAC 50/60HZ OR 125-250VDC	AB	1404-M805A-ENT
17	1	POWERMONITOR 3000, DISPLAY MODULE, WITH 3 METER CABLE	AB	1404-DM
18	1	SHORTING BLOCK, 8 POSITION	FLEX-CORE	IKU8SC
19	1	GROUNDING BAR SYSTEM, 9 POS	SQUARE-D	PK9GTA
20	1	3 POLE FUSE BLOCK - CLASS CC	AB	1492-FB3C30-L