



ITEM	QTY	DESCRIPTION	MFG	CATALOG
1	1	SINGLE DOOR TYPE 12/13 ENCLOSURE 60Hx36Wx12D	HOF	A-603612LP
2	1	PANEL FOR ENCLOSURE 57Hx33W	HOF	A-60P36
3	1	FLOOR STAND KIT 6in. QTY(2)	HOF	AFK0612
4	1	CIRCUIT BREAKER w/THERMAL MAGNETIC TRIP	AB	140U-J2D3-XXX
5	1	ROTARY VARIABLE-DEPTH OPERAT	AB	140U-J-RVMXXX
6	-	-	-	-
7	1	POWER SUPPLY 24VDC 120/230VAC INPUT	AB	1606-XL_-XXX
8	1	PANELVIEW PLUS 600 TOUCH, COLOR, RS-232 Only, DC POWER	AB	2711P-K6C20D
9	1	PUSH BUTTON-MUSHROOM (PUSH-PULL), 40mm RED CAP	AB	800FP-MT44
10	1	EMERGENCY STOP LEGEND 60mm ROUND YELLOW/BLACK TEXT	AB	800F-15YE112
11	1	PUSH BUTTON - MOMENTARY, EXTENDED, RED	AB	800FP-E402
12	1	PUSH BUTTON - MOMENTARY, FLUSH, GREEN	AB	800FP-F301
13	1	PUSH BUTTON - MOMENTARY, FLUSH, BLUE	AB	800FP-F611
14	4	800F MOUNTING LATCH	AB	800F-ALP
15	3	800F CONTACT BLOCK, N.C.	AB	800F-X01
16	3	800F CONTACT BLOCK, N.O.	AB	800F-X10
17	4	CIRCUIT BREAKER, BULLETIN 1492-SP SERIES B 3-POLE	AB	1492-SP3BXXX
18	2	CIRCUIT BREAKER, BULLETIN 1492-SP SERIES C 2-POLE	AB	1492-SP2CXXX
19	1	CIRCUIT BREAKER, BULLETIN 1492-SP SERIES D 1-POLE	AB	1492-SP1DXXX
20	-	-	-	-
21	1	POWERFLEX 4 AC DRIVE 240(208)VAC	AB	22A-XXXXXXX
22	1	POWERFLEX 40 AC DRIVE 240(208)VAC	AB	22B-XXXXXXX
23	1	POWERFLEX 40P AC DRIVE 240(208)VAC	AB	22D-XXXXXXX
24	1	POWERFLEX 400 AC DRIVE 240(208)VAC	AB	22C-XXXXXXX
25	1	COMPACT LOGIX L43 PROCESSOR MODULE	AB	1768-L43
26	1	COMPACT POWER SUPPLY MODULE	AB	1768-PA3
27	1	COMPACT LOGIX ETHERNET BRIDGE MODULE	AB	1768-ENBT
28	1	COMPACT LOGIX 16pt. 24VDC INPUT MODULE	AB	1769-IQ16
29	1	COMPACT LOGIX 16pt. 24VDC OUTPUT MODULE	AB	1769-OB16
30	1	COMPACT LOGIX END COVER RH	AB	1769-ECR
31	-	-	-	-
32	8	END ANCHOR FOR STANDARD 35mm DIN	AB	1492-EAJ35
33	1	POWER DISTRIBUTION TERMINAL	AB	1492-PDM3141
34	4	TERMINAL BLOCK GROUP MARKER FOR 35mm DIN	AB	1492-GM35
35	12	SCREW CONNECTION TERMINAL BLOCK; 1492-J	AB	1492-J4
36	4	SCREW CONNECTION TERMINAL BLOCK; 1492-J	AB	1492-JG4
37	4	END BARRIER; 1492-J	AB	1492-EBJ3
38	-	STANDARD DIN MOUNTING RAIL 35mm	AB	199-DR1
39	-	NARROW SLOT WIRING DUCT 1.5X4in. GRAY	PANDUIT	F15X4LG6
40	-	NARROW SLOT WIRING DUCT 1.5X4in. WHITE	PANDUIT	F15X4WH6
41	-	NARROW SLOT WIRING DUCT COVER 1.5in. GRAY	PANDUIT	C15LG6
42	-	NARROW SLOT WIRING DUCT COVER 1.5in. WHITE	PANDUIT	C15WH6
43	1	8 PORT ETHERNET SWITCH	AB	1783-XXXXX
44	1	MONITORED SAFETY RELAY MSR127	AB	440-XXXXXX