

THIS SPACE INTENTIONALLY LEFT BLANK

XXXX XXXXXXXX XX XXX XXXXXXXXXXXX XX XXXXXXXXXXXX XXXXXXXXXXXX XX XXX XXXXXXXXXXXX XXXXXXXXXXXX XXXXXX XX XXXXXXXXXXXX XXX XXX XXXXXXX XXXXXXX XX XXXXXXXXXXXX	XXXXXX_XXXX XXXXXX	DATASITE RTU FACTORY TALK ME MASTER POWER DISTRIBUTION	DWG XX EXAMPLE	DATE 02-11-09 DWG REV XX
DIST	SHEET 1 OF XX	(PAC)		

8

7

6

5

4

3

2

1

200

201

202

203

204

205

206

207

208

209

210

211

212

213

214

215

216

217

218

219

220

221

222

223

224

225

226

227

228

229

230

231

232

233

234

235

THIS SPACE INTENTIONALLY LEFT BLANK

THIS SPACE INTENTIONALLY LEFT BLANK

D

D

C

C

B

B

A

A


XXXX XXXXXXXX XX XXX XXXXXXXXXXXX XX XXXXXXXXXXXX XXXXXXXXXXXX XX XXXXXXXXXXXX XXXXXXXXXXXX XXXXXX XX XXXXXXXXXXXX XXX XXX XXXXXX XXXXXX XX XXXXXXXXXXXX	XXXXXX_XXXX XXXXXX	DATASITE RTU FACTORY TALK ME MASTER CONTROL SPARE		DWG XX	DATE 02-11-09
		DWT	SHEET 2 OF XX	DWT REV EXAMPLE	DWT REV XX

5

4

3

2



XXXX XXXXXXXX XX XXX XXXXXXXXXXXX
 XX XXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXX
 XX XXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXX
 XXXXXX XX XXXXXXXXXXXXXXXXXXXXXXXX
 XXXXXXX XXXXXXXX XX XXXXXXXXXXXXXXX

XXXXXX_XXXX
XXXXXX

DATASITE RTU
 FACTORY TALK ME MASTER
 DATASITE RTU I/O

DWG NO	DATE	DWG REV
EXAMPLE	02-11-09	XX
SHEET	OF	
3	XX	

8

7

6

5

4

3

2

1

D

D

400

418

401

419

402

420

403

421

404

422

405

423

C

C

406

424

407

425

408

THIS SPACE INTENTIONALLY LEFT BLANK

426

THIS SPACE INTENTIONALLY LEFT BLANK

B

B

409

427

410

428

411

429

A

A

412

430

413

431

414

432

415

433

416

434

417

435

XXXX XXXXXXXX XX XXX XXXXXXXXXXXX
XX XXXXXXXXXXXX XXXXXXXXXXXX
XX XXX XXXXXXXXXXXX XXXXXXXXXXXX
XXXXXXXX XX XXXXXXXXXXXX XXX XXX
XXXXXXXX XXXXXXXX XX XXXXXXXXXXXX

XXXXXX_XXXX
XXXXXX

DATASITE RTU
FACTORY TALK ME MASTER
I/O SPARE

DWG NO XX
DATE 02-11-09
EXAMPLE

DWG REV XX

SHEET 4 OF XX

5

4

3

2

8

7

6

5

4

3

2

1

D

D

C

C


B

B



A

A

PANELVIEW PLUS 600
2711P-T6C20D



RTU/GAS FLOW METER
1758-FL0302



2711-NC13 (SERIAL CABLE)

XXXX XXXXXXXX XX XXX XXXXXXXXXXXX
 XX XXXXXXXXXXXX XXXXXXXXXXXX
 XX XXX XXXXXXXXXXXX XXXXXXXXXXXX
 XXXXXX XX XXXXXXXXXXXX XXX XXX
 XXXXXXX XXXXXXX XX XXXXXXXXXXXX

XXXXXX_XXXX
 XXXXXXX

DATASITE RTU
 FACTORY TALK ME MASTER
 COMMUNICATION DIAGRAM


DWG NO	DATE	DWG REV
EXAMPLE	02-11-09	XX
SHEET	OF	DATE
5	XX	02/11/09

5

4

3

2



ITEM	QTY	DESCRIPTION	MFG	CATALOG
		FACTORY TALK VIEW ME DATASITE RTU PANEL		
1	1	NEMA1 ENCLOSURE 36"x24"x12"	HOFFMAN	CSD362412
2	1	PANEL FOR ENCLOSURE	HOFFMAN	CP3624
3	1	DATASITE ELECTRONIC FLOWMETER, 4-20ma I/O	AB	1758-FL0302
4	1	SOLAR CHARGE CONTROLLER		
5	1	SOLAR PANEL		
6	1	12 VOLT BATTERY		
7	1	FUSE HOLDER 2 POLE, 30A, LED BLOWN FUSE INDICATOR	AB	1492-FB2C30-L
8	2	FUSE, 5 AMP, TIME DELAY, REJECTION TYPE	BUSSMAN	FNQ-R-5
9	1	35mm DIN RAIL	AB	199-DR1
10	1	PANDUIT WIRE DUCT, 1.5" x3" WHITE	PANDUIT	F1.5X3WH6
11	1	PANDUIT WIRE DUCT COVER, 1.5" WHITE	PANDUIT	C1.5WH6
12	-	TERMINAL BLOCK	AB	1492-J4
13	-	END ANCHOR	AB	1492-EAJ35
14	1	PANELVIEW PLUS 600	AB	2711P-T6C20D
15	1	5M (16 FT) RS-232 UPLOAD/DOWNLOAD CABLE	AB	2711-NC13
16	1	12V TO 24V DC CONVERTER		
17	1	CIRCUIT BREAKER, 5 AMP	AB	1489-A1C050
18	1	SELECTOR SWITCH, 2 POSITIONED, MAINTAINED	AB	800H-HR2D1P
19	1	OFF-ON LEGEND PLATE	AB	800H-W133
INSTRUMENTATION DEVICES				
20	1	DIFFERENTIAL PRESSURE SWITCH		
21	1	STATIC PRESSURE SWITCH		
22	1	TEMPERATURE SWITCH		
23	1	PULSE INPUT (TURBINE METERING)		
24	1	HART DEVICE 1		
25	1	HART DEVICE 2		
26	1	HART DEVICE 3		
27	1	HART DEVICE 4		
28	1	HART DEVICE 5		

XXXX XXXXXX XX XXX XXXXXXXXXXXX XX XXXXXXXXXXXX XXXXXXXXXXXX XXXXX XX XXXXXXXXXXXX XXX XXX XXXXXX XXXXXX XX XXXXXXXXXXXX	XXXXXX_XXXX XXXXXX	DATASITE RTU FACTORY TALK ME MASTER RTU PANEL LAYOUT		DWG XX DATE 02-11-09	DWT SHEET 6 OF XX	DWG REV EXAMPLE XX	XX